

# Insert label - EMT (25X6)R - 0817264

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Insert label, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLL, THERMOMARK X, THERMOMARK S1.1, Mounting type: Insert, Cable diameter: 10-25 mm, Lettering field: 25 mm x 6 mm

The figure shows the EMT (40x17)R version

## Key commercial data

<b>package_quantity</b>	1
<b>GTIN</b>	4046356124201

## Technical data

### Dimensions

<b>Length (b)</b>	25 mm
<b>Width (a)</b>	6 mm

### Ambient conditions

<b>Ambient temperature (operation)</b>	-40 °C ... 120 °C
<b>Recommended storage conditions</b>	23 °C / 50 % relative humidity

### General

<b>Color</b>	white
<b>Components</b>	free from silicone and halogen
<b>Material</b>	Polyester
<b>Wipe resistance</b>	DIN EN 61010-1 (VDE 0411-1)
<b>Number of individual labels</b>	5000
<b>Number of individual labels per row</b>	4
<b>RoHS compliant</b>	Yes
<b>Printability</b>	Thermal transfer
<b>Test for substances that would hinder coating with paint or varnish</b>	VW PV 3.10.7:2005-02
<b>Result</b>	Test passed
<b>Test specification weathering-resistance</b>	Following ISO 4892-2:2013-03
<b>Test duration</b>	96 h
<b>Wipe resistance test result</b>	Test passed
<b>Salt spray test specification</b>	DIN EN ISO 9227:2012-09
<b>Test duration</b>	96 h
<b>Salt spray testing result</b>	Test passed

# Insert label - EMT (25X6)R - 0817264

## Technical data

### General

<b>Alternating condensation climate with SO2 test specification</b>	DIN 50018:2013-05
<b>Climate level</b>	AHT 1.0 S
<b>Cycles</b>	2
<b>Condensation test result</b>	Test passed
<b>Foil strength</b>	175 µm
<b>Marking mounting type</b>	Insert

## classifications

### eCl@ss

<b>eCl@ss 4.0</b>	24190219
<b>eCl@ss 4.1</b>	24190219
<b>eCl@ss 5.0</b>	27141137
<b>eCl@ss 5.1</b>	27141137
<b>eCl@ss 6.0</b>	27141137
<b>eCl@ss 7.0</b>	27141137
<b>eCl@ss 8.0</b>	27141137

### ETIM

<b>ETIM 2.0</b>	EC000761
<b>ETIM 3.0</b>	EC000761
<b>ETIM 4.0</b>	EC001530
<b>ETIM 5.0</b>	EC001530

### UNSPSC

<b>UNSPSC 6.01</b>	30211811
<b>UNSPSC 7.0901</b>	39121410
<b>UNSPSC 11</b>	39121410
<b>UNSPSC 12.01</b>	39121410
<b>UNSPSC 13.2</b>	39121410

## accessories

### Ink ribbon

THERMOMARK-RIBBON 110 - 5145384



## Drawings

