MITSUBISHI

GT16 Protective Sheet

User's Manual

GT16-90PSCB GT16-90PSCW GT16-90PSGW GT16-90PSGB GT16-80PSCB GT16-80PSCW GT16-80PSGB GT16-80PSGW GT16-70PSCB GT16-70PSCW GT16-70PSGB GT16-70PSGW GT16-60PSCB GT16-60PSCW GT16-60PSGB GT16-60PSGW

Thank you for purchasing the GOT1000 Series.

Prior to use, please read both this manual and detailed manual thoroughly to fully understand the product.

MODEL	GT16-PS-U
MODEL CODE	1D7M81
IB(NA)-	0800426-B(0901)MFF




●SAFETY PRECAUTIONS●

(Always read these precautions before using this equipment.)

Before using this product, please read this manual and the relevant manuals introduced in this manual carefully and pay full attention to safety to handle the product correctly.

The precautions given in this manual are concerned with this prod-

In this manual, the safety precautions are ranked as "DANGER" and "CAUTION".



Indicates that incorrect handling may cause ♠ DANGER hazardous conditions, resulting in death or

Indicates that incorrect handling may cause A CAUTION hazardous conditions, resulting in medium or slight personal injury or physical damage.

Note that the A CAUTION level may lead to a serious accident

according to the circumstances.

Always follow the precautions of both levels because they are important to personal safety.

Please save this manual to make it accessible when required and always forward it to the end user

[INSTALLATION PRECAUTIONS]

A CAUTION

- When attaching the protective sheet onto the GOT display section, make sure to fit the protective sheet onto the section closely without leaving any air between them. Failure to do so may cause a malfunction
- After attaching the protective sheet, remove the protective film. When the user continues using the GOT with the protective film the film may not be removed.

[STARTUP AND MAINTENANCE PRECAUTIONS]

⚠ CAUTION

 Daily check the protective sheet with eyes. When you find extreme dirt or scratches on the surface, immediately replace i

Using the productive sheet of decreased visibility may cause a malfunction.

[DISPOSAL PRECAUTIONS]

⚠ CAUTION

Dispose of this product as industrial waste.

Manuals

The following shows manuals relevant to this product.

Detailed Manual

	Manual name		Manual number (Model code)
	GT16 User's Manual	(Sold separately)	SH-080778ENG (1D7M88)
(Solid Separately) (1D71vioo)		(Solu separately)	(1D/1000)

Relevant Manuals

For relevant manuals, refer to the PDF manuals stored in the GT Designer2 CD-ROM.

© 2008 MITSUBISHI ELECTRIC CORPORATION

Packing List

After unpacking the box, check that the following products are included.

Model	Product	Quantity
GT16-90PSCB GT16-90PSCB GT16-90PSCW GT16-90PSCW GT16-80PSCB GT16-80PSCB GT16-80PSCW GT16-70PSCB GT16-70PSCB GT16-70PSCB GT16-70PSCW GT16-60PSCB GT16-60PSCB GT16-60PSCB	Protective sheet	5

1. OVERVIEW

This User's Manual describes GT16 protective sheet (hereinafter referred to as the protective sheet).

The following protective sheets are available.
For the applicable GOTs, refer to GT16 User's Manual

Product	Model	Description
Protective sheet	GT16-90PSCB	15" protective sheet Clear
	GT16-90PSGB	15" protective sheet Antiglare
	GT16-90PSCW *1	15" protective sheet Clear (Frame: White)
	GT16-90PSGW *1	15" protective sheet Antiglare (Frame: White)
	GT16-80PSCB	12.1" protective sheet Clear
	GT16-80PSGB	12.1" protective sheet Antiglare
	GT16-80PSCW *1	12.1" protective sheet Clear (Frame: White)
	GT16-80PSGW *1	12.1" protective sheet Antiglare (Frame: White)
	GT16-70PSCB	10.4" protective sheet Clear
	GT16-70PSGB	10.4" protective sheet Antiglare
	GT16-70PSCW *1	10.4" protective sheet Clear (Frame: White)
	GT16-70PSGW *1	10.4" protective sheet Antiglare (Frame: White)
	GT16-60PSCB	8.4" protective sheet Clear
	GT16-60PSGB	8.4" protective sheet Antiglare
	GT16-60PSCW *1	8.4" protective sheet Clear (Frame: White)
	GT16-60PSGW *1	8.4" protective sheet Antiglare (Frame: White)
*1 For the	white frame (other th	an the display section) use the


*1 For the white frame (other than the display section), use the

Use the protective sheet to protect the display section surface from scratches and dirt when operating the touch keys on the GOT display

Select a clear protective sheet for the display intensity, or select an antiglare protective sheet for antireflection


2. PART NAMES AND EXTERNAL **DIMENSIONS**

(1) 15"/12.1" protective sheet



Item	Α	В
15" Protective sheet	391 (15.4)	290 (11.4)
12.1" Protective sheet	310 (12.2)	236 (9.3)
	Hr	it mm (inch


(2) 10.4"/8.4" protective sheet




Item	Α	В
10.4" Protective sheet	297 (11.7)	208 (8.2)
8.4" Protective sheet	235 (9.3)	184 (7.3)
	Ur	nit: mm (inch)

3. INSTALLATION PROCEDURE

Remove the old protective sheet from the GOT if the sheet is attached, and clean the GOT surface. (Peel off the sheet slowly.)




2) Remove the release paper from the back of a new protective sheet. Do not remove the protective film. Attach the protective sheet so that the sheet does not overlap with the USB environmental protection cover on the GOT.



3) For attaching the protective sheet, make sure to fit the sheet on the GOT without wrinkles or air between the sheet and the GOT.



Remove the protective film from the protective sheet. When the user continues using the GOT with the protective film the film may not be removed.



Warranty

Italy

Mitsubishi will not be held liable for damage caused by factors found not to be the cause of Mitsubishi; machine damage or lost profits caused by faults in the Mitsubishi products; damage, secondary damage, accident compensation caused by special factors unpredictable by Mitsubishi; damages to products other than Mitsubishi products; and to other duties.

⚠ For safe use

- This product has been manufactured as a general-purpose part for general industries, and has not been designed or manufactured to be incorporated in a device or system used in purposes related to
- Before using the product for special purposes such as nuclear power, electric power, aerospace, medicine or passenger movement vehicles, consult with Mitsubishi. This product has been manufactured under strict quality control.
- However, when installing the product where major accidents or losses could occur if the product fails, install appropriate backup or failsafe functions in the system.

Country/Region	Sales office/Tel
U.S.A	Mitsubishi Electric Automation Inc.
	500 Corporate Woods Parkway Vernon Hills, IL 60061, U.S.A. Tel: +1-847-478-2100
Brazil	MELCO-TEC Rep. Com.e Assessoria Tecnica Ltda.
	Rua Correia Dias, 184, Edificio Paraiso Trade Center-8 andar
	Paraiso, Sao Paulo, SP Brazil
_	Tel: +55-11-5908-8331
Germany	Mitsubishi Electric Europe B.V. German Branch
	Gothaer Strasse 8 D-40880 Ratingen, GERMANY
	Tel: +49-2102-486-0
U.K	Mitsubishi Electric Europe B.V. UK Branch
	Travellers Lane, Hatfield, Hertfordshire., AL10 8XB, U.K.
	Tel: +44-1707-276100
Dr. C	THE STATE OF THE S

lei: +44-1707-276100
Mitsubish Electric Europe B.V. Italian Branch
Centro Dir. Colleoni, Pal. Perseo-Ingr.2
Telescope Burger Colleoni, Pal. Perseo-Ingr.2
Telescope Burger Colleonia Colle E-08190 Sant Cugat del Valles, Barcelona, Spain Tel: +34-93-565-3131 Mitsubishi Electric Europe B.V. French Branch 25, Boulevard des Bouvets, F-92741 Nanterre Cedex, France TEL: +33-1-5568-5568 France

TEL: +33-1-3000-3000 Circuit Breaker Industries Ltd. Private Bag 2016, ZA-1600 Isando, South Africa Tel: +27-11-928-2000 Mitsubishi Electric Automation (Hong Kong) Ltd. 40th Flora Manuffor Towar 160 Electric South Africa Hong Kong

10th Floor, Manulife Tower, 169 Electric Road, North Point, Hong Kong Tel: +852-2887-8870 Tiel: +652-2887-8870 Model Tiel: +652-2887-8870 Model Tiel: +652-2887-8870 Model Tiel: +652-2887-8870 Model Tiel: +652-1880 Model Thomas Road, 44F Zuhar Pielzz-, No. 80 Xin Chang Road, 44F Zuhar Zuh China

Korea

Singapore

Tel:+82-2-3660-9552
Mitsubishi Electric Asia Pte, Ltd.
307 Alexandra Road #05-01/02,
Mitsubishi Electric Building, Singapore 159943
Tel:+65-6470-2460
Mitsubishi Electric Automation (Thailand) Co., Ltd.
Mitsubishi Electric Automation (Thailand) Co., Ltd.
Bang-Chan Industrial Estate No.111 Moo 4, Serithai I
T.Kannayao, A.Kannayao, Bangkok 10230 Thailand
Tel:+66-2-517-1326
P.T. Autoteknindo Sumber Makmur
Muara Karana Selatan Block AUtara Indonesia

P.T. Autoteknindo Sumber Makmur Muara Karang Selatan, Block A'Ultara No.1 Kav. No.11 Kawasan Industri Pergudangan Jakarta - Ulara 14440, P.O.Box 5045 Jakarta, 11050 Indonesia Tel: +622-16503083 Messung Systems Pvt, Ltd. Electronic Sadan NO:III Unit No15, M.I.D.C Bhosari, Pune-411026, India Tel: +91-20-2712-3130 Mitsubishi Electric Australia Pty. Ltd. 348 Victoria Road, Rydalmere, N.S.W 2116, Australia Tel: +61-2-9684-7777

India Australia

★MITSUBISHI ELECTRIC CORPORATION HEAD OFFICE : TOKYO BUILDING, 2-7-3 MARUNOUCHI, CHIYODA-KU, TOKYO 100-8310, JAPAN NAGOYA WORKS : 1-14, YADA-MINAMI 5-CHOME, HIGASHI-KU, NAGOYA, JAPAN

When exported from Japan, this manual does not require application to the Ministry of Economy, Trade and Industry for service transaction permission.

Specifications subject to change without notice Printed in Japan.